

VISIT US AT OUR BOOTH L3107



SEMICON[®]
SOUTHEAST
ASIA **30** YEARS
Special Edition

MAY 20-22, 2025
SANDS EXPO &
CONVENTION CENTRE
SINGAPORE



STRONGER
TOGETHER



New

QC2 Dispense Head 2.0

- With **torque protection**, so will not be overtightened.
- Internally **PFA lined**.
- **Priming Function**: to recirculate chemical after container hook up to remove air bubbles.
- Various options for **integrated sensors** (e.g. bubble switch, limit switch, overfill alarm sensor).

Over 100 Dispense Head Variants



New



High purity
plastics

TANK QUICK COUPLING

CHEMICAL RESISTANT QUICK COUPLINGS

self-sealing, no dead spaces,
no contamination.

Fast and easy connection.



Digital key-code to prevent mix-ups.



High flow rates for fast emptying.



Dry disconnection.



Ultra-pure plastics, no wetted metal parts.



New

QC-Guard

Our safest Dip Tube Cap!



LOW HEIGHT

Minimizes the risk of being sheared off during forklift handling.

MORE CLEANLINESS

Protects the dip tube from dust and dirt during transport.

DOUBLE PROTECTION

Seals the dip tube with a tight cap in addition to the primary „S“ closure.

TAMPER-PROOF MARKING

The seal can be marked with your logo to ensure that you have closed the container.

Individual Serial Numbers



Advantages

Makes it easy to read and track the serial number. Simply enter and retrieve in any browser.

Specification available at any time!


SPECIFICATION		CIS QC SYSTEM	
GENERAL			
Art. No. / PE	218ABCDE		
QF-ALPES-QS-0300-07			
QF code no.	355463	Batch no.	1128964
Date of introduction	06/03/2015		
FIGURE			
DETAILS		DETAILS	
Product Code	QC2	Ring Thread Type	M6x1.0
Material	Styropor 5147 PE w/ PE o-ring	Material	HDPE
Product PE	Profile gasket PE	Product PE	UP transponder incorporated
Accessories		Accessories	



RFID CHIP

Chemical, Batch and Container-Data

Simply added



- Confusion proof digital coding.
- 100% traceable.
- Easy integration into existing supply chains.



GPS Cap



MAKES CONTAINERS SMART AND CHEMICAL HANDLING SAFE



Locate containers with GPS.



Temperature monitoring.



Shock sensor.



Fits perfectly in all containers.

ELECTRONICS FULLY
ENCAPSULATED

NO CONTACT
WITH THE CHEMICALS

BATTERY CAN BE
RECHARGED WIRELESSLY

ROBOTIC SYSTEM for Filling & Dispense

- No more chemical contact.
- No more chemical mix-up.
- No contamination.

Play it safe with your robot colleague!





SAMPLING CUBE

ULTRA-CLEAN SAMPLING
FAST, SIMPLE AND SAFE



Fully automatic dispensing at the push of a button.



Closed loop without outgassing and contamination.



Media contact only with qualified PFA tubing and sampling bottle.



For drum, IBC, canister and tank.

THANK YOU FOR YOUR ATTENTION !

AS Strömungstechnik GmbH
Elly-Bernhorn Str 7
73760 Ostfildern Germany
+49 (0) 711 220 548-29
info@asstroemungstechnik.de
www.asstroemungstechnik.de



Asia: Dusemund Pte Ltd
25 International Business Park
#04-112 German Centre Singapore 609916
claus@dusemund.com
www.dusemund.com

DUSEMUND PTE LTD
High Tech Solutions

